

# Rittal – The System.

Faster – better – everywhere.



## SZ 4139.140 Prilagodljiva luč

State: 12.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 4139.140 - Prilagodljiva luč

Supply voltage: 100 - 240 V AC 50/60 Hz

## Features

Št. Modela	SZ 4139.140
Zasnova	brez stikala za vrata
Obseg dobave	Prilagodljiva luč Luči Pokrov luči Sestavni deli
Poraba energije	14 W
Ballast	Wide-range electronic ballast
Možnosti priklopa	Power supply via connectors Door-operated switch Through-wiring (creating rows of lights)
Luči	Fluorescent lamp, base G13
Razred zaščite	I (PE conductor)
Stikalo (tip)	Integral on/off/door-operated switch
Light cover	Yes
Luči – vrsta namestitve	Screw-fastening
Rated impulse withstand voltage, phase to earth	1000 V AC
Nazivna impulzna vzdržna napetost, med fazami	500 V AC
Nazivna izolacijska napetost	500 V DC/1s

# Features

Možnosti namestitve	TS vodoravni profil strešnega okvirja: neposreden Navpični profil TS, SE: z adapterskim nosilcem TS SE profili na sprednjem in zadnjem delu strešnega okvirja: z adapterskim nosilcem TS SE profili na strani strešnega okvirja: neposredni AE, CM, TP: z univerzalnim nosilcem AE: s tirnico za notranjo montažo
Mere	Širina: 452 mm Višina: 117 mm Globina: 50 mm
Delovno temperaturno območje	-15 °C...45 °C
Vtičnice	D, earthing-pin (type F, CEE 7/4)
Temperaturno območje shranjevanja	-20 °C...70 °C
Nazivna delovna napetost	100 V - 240 V, 1~, 50 Hz/60 Hz
Različica vtičnice	D, earthing-pin (type F, CEE 7/4)
Paketi	1 pc(s).
Neto teža	1,2 kg
Bruto teža	1,243 kg
Carinska tarifna številka	94054990
ECLASS 8.0	27189241
Opis izdelka	SZ Courtesy light, WHD: 452x117x50 mm, 14 W, 100-240 V, 50/60 Hz, without door operated switch, with earthing-pin socket

# Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	-----------------------------------------------------------