

Rittal – The System.

Faster – better – everywhere.



SZ 4155.110 Univerzalna luč

State: 22.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4155.110 - Univerzalna luč z vgrajenim detektorjem gibanja

Enclosure light with insulated plastic housing, motion detector and voltage supply 110 - 240 V AC 50/60 Hz.



Features

Št. Modela	SZ 4155.110
Prednosti	Enostavna in hitra namestitvev
Material	Plastika
Obseg dobave	Univerzalna luč Integrirani detektor gibanja Luči Pokrov luči Sestavni deli
Poraba energije	18 W
Ballast	Wide-range electronic ballast
Možnosti priklopa	Power supply via connectors Through-wiring (creating rows of lights)
Integrated motion sensor	Yes
Luči	Compact fluorescent lamp, base 2G11
Razred zaščite	I (PE conductor)
Stikalo (tip)	Integral, on/off/motion detector mode
Light cover	Yes

Features

Luči – vrsta namestitve	Screw-fastening
Nazivna impulzna vzdržna napetost, med fazami	2500 V AC
Nazivna izolacijska napetost	250 V AC
Možnosti namestitve	TS vodoravni profil strešnega okvirja: neposreden Navpični profil TS, SE: z adapterskim nosilcem TS SE profili na sprednjem in zadnjem delu strešnega okvirja: z adapterskim nosilcem TS SE profili na strani strešnega okvirja: neposredni AE, CM, TP: z univerzalnim nosilcem AE: s tirnico za notranjo montažo
Mere	Širina: 345 mm Višina: 95 mm Globina: 55 mm
Delovno temperaturno območje	-15 °C...45 °C
Vtičnice	1 x D, earthing-pin (type F, CEE 7/3)
Temperaturno območje shranjevanja	-20 °C...70 °C
Nazivna delovna napetost	110 V - 240 V, 1~, 50 Hz/60 Hz
Različica vtičnice	D, earthing-pin (type F, CEE 7/3)
Paketi	1 pc(s).
Neto teža	0,714 kg
Bruto teža	0,92 kg
Carinska tarifna številka	94054990
ECLASS 8.0	27189241
Opis izdelka	SZ Universal light, WHD: 343x95x55 mm, 18 W, 110-240 V, 50/60 Hz, with integral motion detector, with earthing-pin socket, VDE

Approvals

Approvals

Explanations

Declaration of conformity

Declaration of conformity UK