

Rittal – The System.

Faster – better – everywhere.



SZ 4169.000

Luknjani profil 23 x 23 mm

State: 4.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4169.000 - Luknjani profil 23 x 23 mm za VX, TS, VX SE

Za namestitev na vodoravne in navpične dele ohišja z dodatnimi montažnimi komponentami.



Features

Št. Modela	SZ 4169.000
Material	Jeklena pločevina
Površinska obdelava	Pocinkano
Dolžina	295 mm
Možnosti namestitve	<p>V VX na navpičnem in vodoravnem delu ohišja z uporabo montažnih nosilcev TS</p> <p>V VX SE, na navpičnem delu ohišja prek montažnih nosilcev skupaj z adaptersko letvijo VX</p> <p>V VX SE, na vodoravnem profilu/v strehi prek montažnih nosilcev skupaj z adaptersko letvijo VX v globino.</p> <p>On the vertical enclosure section: Directly via support brackets TS, via adaptor rail for PS compatibility in conjunction with angle brackets, mounting brackets or support brackets PS</p> <p>On the horizontal enclosure section: Directly via angle brackets, mounting brackets or support brackets PS</p>
Primerno za	<p>Vrsta ohišja: VX</p> <p>TS</p> <p>VX SE</p> <p>Suitable for width or height or depth: 400 mm</p>
Paketi	12 pc(s).
Neto teža	2,052 kg

Features

Bruto teža	2,22 kg
PCF na paket (od zibelke do vrat)	11,45 kg CO2 eq (Cat B)
Opomba o kategoriji PCF	Kategorija B: PCF vrednost (od zibelke do vrat) na podlagi teže izdelka, približno izračunana in samodeklarirana
Carinska tarifna številka	73269098
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189234
Opis izdelka	SZ Punched rail 23 x 23 mm, for TS, SE, for WHD: 400 mm, L: 295 mm

Approvals

Explanations	PCF-declaration
--------------	-----------------