

Rittal – The System.

Faster – better – everywhere.



SZ 4175.000

Luknjani profil 23 x 23 mm

State: 23.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 4175.000 - Luknjani profil 23 x 23 mm za VX, TS, VX SE

Za namestitev na vodoravne in navpične dele ohišja z dodatnimi montažnimi komponentami.



Features

Št. Modela	SZ 4175.000
Material	Jeklena pločevina
Površinska obdelava	Pocinkano
Dolžina	1.495 mm
Možnosti namestitve	On the vertical enclosure section: Directly via support brackets TS, via adaptor rail for PS compatibility in conjunction with angle brackets, mounting brackets or support brackets PS On the horizontal enclosure section: Directly via angle brackets, mounting brackets or support brackets PS
Primerno za	Vrsta ohišja: VX TS VX SE Suitable for width or height or depth: 1.600 mm
Paketi	6 pc(s).
Neto teža	5,394 kg
Bruto teža	5,677 kg
PCF na paket (od zibelke do vrat)	29,09 kg CO2 eq (Cat B)
Opomba o kategoriji PCF	Kategorija B: PCF vrednost (od zibelke do vrat) na podlagi teže izdelka, približno izračunana in samodeklarirana

Features

Carinska tarifna številka	73269098
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189234
Opis izdelka	SZ Punched rail 23 x 23 mm, for TS, SE, for WHD: 1600 mm, L: 1495 mm

Approvals

Explanations	PCF-declaration
--------------	-----------------