

Rittal – The System.

Faster – better – everywhere.



PS 4638.600

Utility lectern

State: 12.2.2026 (Source: rittal.com/si-sl)



FRIEDHELM LOH GROUP

PS 4638.600 - Utility lectern for VX, TS, VX SE, TP, PC

For programming units etc., prepared for mounting on the tubular door frame. When required for servicing, it folds down quickly with a maximum support area, and after use is stowed away in a space-saving design.



Features

Model No.	PS 4638.600
Product description	For programming units etc., prepared for mounting on the tubular door frame. When required for servicing, it folds down quickly with a maximum support area, and after use is stowed away in a space-saving design.
Material	Sheet steel
Colour	RAL 7035
Support area	Width: 413 mm Depth: 400 mm
To fit door width	600 mm
Installation options	On the tubular door frame For external mounting on surfaces.
Load capacity	max. 300 N
Support area	Width: 413 mm Depth: 400 mm

Features

To fit	Enclosure type: VX TS VX SE PC
Packs of	1 pc(s).
Net weight	3.471
Gross weight	3.671
PCF per pack (cradle-to-gate)	14.5 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
EAN	4028177107496
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504