

Rittal – The System.

Faster – better – everywhere.



VX 5301.246

Side panel, vertically divided

State: 7.8.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 5301.246 - Side panel, vertically divided for VX IT

Side panels, vertically divided, for VX IT



Features

Model No.	VX 5301.246
Benefits	Easy to use Easy to close with snap fasteners Optimum access to all installed components Opening is only possible via internal locking elements, which requires free access via the doors, but significantly increases access security Individual side parts may be completely dismantled at any time without the need for tools
Material	Sheet steel
Surface finish	Powder-coated
Colour	RAL 7035
Supply includes	2 side parts Punched rail 6 Hinges 4 quick-release fasteners Assembly parts
Assembly instruction	Access via the front and rear doors must be guaranteed
To fit	Enclosure type: VX IT Height: = 2,000 mm Depth: = 800 mm

Features

IP protection category to IEC 60529	IP 20
Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	22.5
Gross weight	24.5
PCF per pack (cradle-to-gate)	87.6 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
EAN	4028177955875
E-Number Sweden	E7282561
ETIM 9	EC002524
ECLASS 8.0	27182101