

Rittal – The System.

Faster – better – everywhere.



IT 5302.026 Kombinirane tirnice

State: 23.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 5302.026 - Kombinirane tirnice za 482,6 mm (19")

Features

| | |
|-----------------------------------|--|
| Št. Modela | IT 5302.026 |
| Aplikacije | Za napeljavo kablov in razbremenitev napetosti na 482,6 mm (19") nivoju |
| Material | Jeklena pločevina |
| Površinska obdelava | Pocinkano |
| Obseg dobave | Montažni deli za kombinirano tirnico, brez montažnih delov za pritrditev kablov |
| Možnosti namestitve | Znotraj 482,6 mm (19") montažne ravni, na 482,6 mm (19") sistemskih luknjah |
| Mere | Višina: 1 U |
| Primerno za | Vrsta ohišja: TS IT VX IT TX CableNet |
| Paketi | 4 pc(s). |
| Neto teža | 1,348 kg |
| Bruto teža | 1,4 kg |
| PCF na paket (od zibelke do vrat) | 5,2 kg CO2 eq (Cat B) |
| Opomba o kategoriji PCF | Kategorija B: PCF vrednost (od zibelke do vrat) na podlagi teže izdelka, približno izračunana in samodeklarirana |
| Carinska tarifna številka | 83024200 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Opis izdelka | Combination rail, 1 U, for 482.6 mm (19"), for cable routing and strain relief at the 19" level, for installation within the 19" mounting level or at the 19" system punchings |