

Rittal – The System.

Faster – better – everywhere.



PC 5386.000

PC sistem ohišij

State: 11.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



PC 5386.000 - PC sistem ohišij

Secure accommodation of all PC components, from monitors, to PCs, to keyboards. For ultimate ease of operation in a modern design. Perfect protection from humidity and dirt, temperature fluctuations and unauthorised access.

Features

Št. Modela	PC 5386.000
Zasnova	s steklenimi vrati na vrhu, predalom za tipkovnico in polico za komponente
Material	Ohišje, vrata, zadnja vrata, montažni prostor, nosilci: jeklena pločevina Ročaji, okrasne obrobe: plastika Obrobe vrat: aluminij Nadzorno okno: enoslojno varnostno steklo
Površinska obdelava	Ohišje in vrata: temeljni premaz, prašno barvana zunanost, teksturirana barva Montažni prostor, nosilec: prašno barvano
Barva	Ohišje, vrata, okrasne obrobe, nosilci: RAL 7035 Ročaj: podobno RAL 9006 Zaslona, sredinski del vrat: RAL 7015
Obseg dobave	Ohišje, vrata, zadnja vrata Steklena vrata, zgoraj Predal za tipkovnico Polica za komponente
Mere	Širina: 800 mm Višina: 1.600 mm Globina: 636 mm
IP razred zaščite po IEC 60 529	IP 55
Razred zaščite NEMA	NEMA 12
Maks. mere tipkovnice (ŠxVxG)	480 x 70 x 260 mm
Osnovni material	Sheet steel
Paketi	1 pc(s).

Features

Neto teža	123,4 kg
Bruto teža	126 kg
Carinska tarifna številka	94032080
ECLASS 8.0	27180501
Opis izdelka	PC PC enclosure system, WHD: 800x1600x600 mm, Sheet steel, with glazed door at the top, keyboard drawer, component shelf

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK