

Rittal – The System.

Faster – better – everywhere.



DK 5501.935

Air baffle plates for TS IT 482.6 mm (19") mounting frames

State: 11.12.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.935 - Air baffle plates for TS IT 482.6 mm (19") mounting frames

To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.



Features

Model No.	DK 5501.935
Product description	With all-round brush strip for collision-free shielding with installed rail systems on the outer mounting level.
Applications	To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.
Material	Sheet steel Blanking panel: Plastic, UL 94-HB, halogen-free Brush strip: Plastic, UL 94-HB
Surface finish	Spray-finished
Colour	RAL 9005
Supply includes	2 vertical trim panels 2 horizontal trim panels 4 brush strips Assembly parts 2 blanking panels, 3 U
Assembly instruction	The vertical and horizontal trim panels with brush strip may be fitted on both the front and rear 482.6 mm (19") mounting frame for partitioning.

Features

To fit	Width: 800 mm Height: 2,200 mm
Packs of	1 pc(s).
Net weight	7.01
Gross weight	7.31
Customs tariff number	73269098
EAN	4028177706910
E-Number Sweden	E7239985
ETIM 9	EC000331
ECLASS 8.0	27189272