

Rittal – The System.

Faster – better – everywhere.



DK 5502.100 Kabelski kanal

State: 22.5.2026 (Source: rittal.com/si-si)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5502.100 - Kabelski kanal za TS IT

Cable duct with removable duct cover hinged on both sides.



Features

Št. Modela	DK 5502.100
Prednosti	Enostavna montaža s hitrim pritrdjevanjem brez orodja Visoka gostota zaradi napeljave kablov v obliki črke U Primerno za povezovanje hrbet ob hrbtu Kabelski kanal se lahko uporablja kot zaščitni element za preprečevanje kratkih stikov zraka znotraj hladnega hodnika Zaklepne kabelske uvodnice se lahko z montažnimi deli namestijo na standardne montaže 1 U
Material	Jeklena pločevina Plastika po UL 94-HB
Barva	RAL 9005
Obseg dobave	Pokrov in montažni deli vključno s 4 držali za nadomestne kable
Možnosti namestitve	V TS IT z montažnimi kotniki 482,6 mm (19"), višina 2000 mm V TS IT z montažnim okvirjem 482,6 mm (19"), višina 1800 mm V TE 8000 z montažnim okvirjem 482,6 mm (19"), višina 2000 mm V Data Rack s 40 U
Enote	38 U
Mere	Širina: 95 mm Višina: 1.689 mm Globina: 150 mm
Paketi	1 pc(s).

Features

Neto teža	7,8 kg
Bruto teža	8,16 kg
Carinska tarifna številka	73269098
ETIM 9	EC000012
ECLASS 8.0	27400703
Opis izdelka	DK Cable duct, 38 U, for TS IT, Height 1800 mm: with mountingframe, Height 2000 mm: with profiles