

Rittal – The System.

Faster – better – everywhere.



DK 5502.120 Kabelski kanal

State: 23.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5502.120 - Kabelski kanal za TS

For cable clamping and routing with network and server applications.



Features

Št. Modela	DK 5502.120
Prednosti	Enostavna montaža s hitrim pritrditvijo brez orodja Alternativno primerno za pritrditev z vijaki Večnamenske luknje za dodatke za urejanje kablov
Aplikacije	Za vpenjanje in usmerjanje kablov v omrežnih in strežniških aplikacijah
Material	Jeklena pločevina
Barva	RAL 9005
Opomba	Montaža po celotni globini s širino 800 mm, pri širini 600 mm pa samo za drugim 482,6 mm (19") nivojem.
Mere	Širina: 115 mm
Dolžina	2.000: 2.200 mm
Paketi	1 pc(s).
Neto teža	3,6 kg
Bruto teža	3,88 kg

Features

Carinska tarifna številka	83024200
ETIM 9	EC000012
ECLASS 8.0	27400703
Opis izdelka	DK Cable route, WxH: 115x2000 mm, For TS, RAL 9005
