

Rittal – The System.

Faster – better – everywhere.



DK 5502.145 Kabelski kanal

State: 21.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5502.145 - Kabelski kanal za TS IT, TE

Cable duct with removable duct cover hinged on both sides.



Features

Št. Modela	DK 5502.145
Prednosti	Enostavna montaža s hitrim pritrdjevanjem brez orodja Visoka gostota zaradi napeljave kablov v obliki črke U Primerno za povezovanje hrbet ob hrbtu
Material	Jeklena pločevina Plastika po UL 94-V0
Barva	RAL 9005
Obseg dobave	Pokrov in montažni deli vključno s 4 držali za nadomestne kable
Enote	42 U
Primerno za	Vrsta ohišja: TS IT TE Širina: 800 mm Višina: 2.200 mm
Primerno za širino	800 mm
Paketi	1 pc(s).
Neto teža	8,298 kg
Bruto teža	8,735 kg
Carinska tarifna številka	73269098
ECLASS 8.0	27400604

Features

Opis izdelka

DK Cable duct, WxH: 800x2200 mm, 42 U, For TS IT, RAL 9005