

Rittal – The System.

Faster – better – everywhere.



DK 5502.255

Cable management panel with brush strip

State: 1.2.2026 (Source: ittal.com/si-si)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5502.255 - Cable management panel with brush strip 482.6 mm (19")

With cut-out 390 x 40 mm (2 U) or 390 x 20 mm (1 U) with brush insert, accommodation facility for cable clamp straps.



Features

Model No.	DK 5502.255
Product description	For convenient, simple cable routing between two areas separated by a 482.6 mm (19") mounting level, for example, between the front and rear areas of the 482.6 mm (19") mounting level.
Applications	For locking and simultaneous cable routing in installation zones to the 1 U, 482.6 mm (19") mounting standard
Material	Sheet steel Brush strip: Plastic, UL 94-HB
Surface finish	Spray-finished
Colour	RAL 9005
Mounting cut-out	Width: 390 mm Height: 20 mm
Dimensions	Width: 482.6 mm
Units	1 U
Packs of	1 pc(s).
Net weight	0.2
Gross weight	0.486

Features

Customs tariff number 73269098

EAN 4028177679368

E-Number Sweden E7239792

ETIM 9 EC000322

ECLASS 8.0 27400604