

Rittal – The System.

Faster – better – everywhere.



SE 5830.500

Sistem samostojećih ohišij SE 8

State: 21.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SE 5830.500 - Sistem samostojećih ohišij SE 8

Individual sheet steel enclosure with stable enclosure body, two integrated mounting levels, screw-fastened rear panel and door. Roof and sides from a single piece with roll-formed frame. Fully compatible interior installation with the TS 8, enabling full integration into the TS 8 product family. Enclosure widths ranging from 600 to 1800 mm Time-saving assembly work due to the roll-formed side panels



Features

Št. Modela	SE 5830.500
Material	Ohišje: jeklena pločevina 1,5 mm Vrata: jeklena pločevina, 2,0 mm Zadnja plošča: jeklena pločevina, 1,5 mm Plošče z uvodnicami: jeklena pločevina, 1,5 mm Montažna plošča: jeklena pločevina, 3,0 mm
Površinska obdelava	Ohišje, vrata in zadnja plošča: temeljni premaz, prašno barvna zunanost, teksturirana barva Montažna plošča in plošče z uvodnicami: pocinkano
Barva	RAL 7035
Obseg dobave	Ohišje, zaprt zgornji del in stranice Vrata Zapiranje vrat pri enokrilih ohišjih, možnost zamenjave na nasprotno stran Montažna plošča Kabelske uvodnice Zadnja plošča, snemljiva Ključavnica: 3 mm dvojna ključavnica 2 luknjani tirnici TS 18 x 38 mm Zadnja plošča, enodelna

Features

Mere	Širina: 600 mm Višina: 1.800 mm Globina: 400 mm
Mere montažne plošče (Š x V)	499 mm x 1.696 mm
Razred zaščite po IEC 60 529	IP 55
Razred zaščite NEMA	NEMA 12 NEMA 3R
IK koda	IK10
Število vrat	1
Osnovni material	Sheet steel
Paketi	1 pc(s).
Neto teža	94 kg
Bruto teža	97 kg
Carinska tarifna številka	94032080
ECLASS 8.0	27180101
Opis izdelka	SE Free-standing enclosure system, WHD: 600x1800x400 mm, Sheet steel, with mounting plate, single door at the front

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK