

Rittal – The System.

Faster – better – everywhere.



CP 6206.420

Nagibni adapter $\pm 45^\circ$

State: 13.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6206.420 - Nagibni adapter $\pm 45^\circ$ za priključek nosilne roke $\varnothing 130$ mm

Za namestitev med sklopko sistema 60/120 ali priključek, sistem 60/120 ali kotno sklopko 90° , sistem 60/120 in nadzorno ploščo.

Features

Št. Modela	CP 6206.420
Prednosti	Notranji zobati tečaj omogoča stabilno zaklepanje nagnjenega ohišja v različnih položajih. Z vstavitvijo navojnih zatičev (priloženih) je mogoče omejiti kot vrtenja.
Aplikacije	Za priklop nadzorne plošče na nagibni adapter Sponka CP 60/120/180 za priključek nosilne roke $\varnothing 130$ mm, 6206.300, 6212.300, 6218.300 Priključek CP 60/120 za priključek nosilne roke $\varnothing 130$ mm, 6206.320, 6212.320 Kotna sponka 90° , CP 60/120, 6206.380, 6212.380
Material	Nagibni adapter: lito aluminijasto Meh: plastika
Barva	RAL 7024
Obseg dobave	Tesnila Oddelek za meh Sestavni deli
Vrtenje/nagibanje	Yes
Tilt angle note	Nastavljivo v korakih po $7,5^\circ$
Paketi	1 pc(s).
Neto teža	1,35 kg
Bruto teža	1,42 kg
Carinska tarifna številka	76169990
ETIM 9	EC000882

Features

ECLASS 8.0	27400556
------------	----------

Opis izdelka	CP Tilting adaptor 45°, CP 60/120, for support arm connection Ø 130 mm
--------------	--

Approvals

Explanations	Manufacturer's declaration
--------------	----------------------------