

Rittal – The System.

Faster – better – everywhere.



CP 6206.480

Connection console VESA 75/100

State: 30.8.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6206.480 - Connection console VESA 75/100

For rear connection of flat command panels, standard TFTs and industrial PCs with VESA 75/100 connection. May be connected to Rittal support arm systems CP 40 and CP 60, and also CP 120 by using an adaptor from support arm connection Ø 130 mm to rectangular 120 x 65 mm.



Features

Model No.	CP 6206.480
Design	Connection to Rittal support arm systems
Product description	For rear connection of flat command panels, standard TFTs and industrial PCs with VESA 75 / 100 connection.
Benefits	Fast, simple one-man assembly using machined keyholes More space for installation and servicing Cables may be routed to devices outside and below the console Removable cover for simple cable routing and access to interior device connections Integral cable clamping facilities Cover and captive screws
Material	Die-cast zinc
Colour	Connection console: RAL 7035 Cover: RAL 7024
Supply includes	Seal and assembly parts Cable ties for cable clamping
Rifid y/n	Yes
Note	Depending on the application, an attachment, coupling or adaptor are required
Load capacity	800 N

Features

Packs of	1 pc(s).
Net weight	2.5
Gross weight	2.775
Customs tariff number	85444290
EAN	4028177693920
ETIM 9	EC002622
ECLASS 8.0	27189263

Approvals

Explanations	Manufacturer's declaration
--------------	----------------------------