


Rittal – The System.

Faster – better – everywhere.



SM 6450.050

Napajalnik

State: 13.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SM 6450.050 - Napajalnik Za TFT zaslon

Z vtičnico IEC320, s kablom (1,5 m) za priklop na TFT zaslon.

Features

Št. Modela	SM 6450.050
Material	Ohišje: plastika
Obseg dobave	Napajalnik s priključkom IEC 60 320 C14 Integriran kabel (1,5 m) za povezavo s TFT zaslonom
Mere	Širina: 112 mm Višina: 31 mm Globina: 47 mm
Vhodna napetost	100 - 240 V
Izhodna napetost	12 V DC
Delovno temperaturno območje	10 °C...40 °C
Temperaturno območje shranjevanja	-10 °C...80 °C
Paketi	1 pc(s).
Neto teža	0,254 kg
Bruto teža	0,294 kg
Carinska tarifna številka	85043121
ETIM 9	EC001781
ECLASS 8.0	19089213
Opis izdelka	SM Power pack, For TFT-Monitor, Input voltage: 100-240 V, Ausgang: 12 V, L: 1,5 m