

# Rittal – The System.

Faster – better – everywhere.



## CP 6538.000

# Ohišje nadzorne plošče z vrati

State: 1.7.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CP 6538.000 - Ohišje nadzorne plošče z vrati

Command panel housing with door, sheet steel, with aluminium handle strips. Door opening on the front. Protection category IP 55. Cut-out and reinforcement for CP-L support arm system, Ø 130 mm.

## Features

Št. Modela	CP 6538.000
Material	Ohišje in vrata: jeklena pločevina Ročaji: aluminij Pokrovčki: plastika
Površinska obdelava	Ohišje in vrata: temeljni premaz, prašno barvana zunanost, teksturirana barva Ročaji: prašno barvano
Barva	Ohišje in vrata: RAL 7035 Ročaji in pokrovčki: RAL 5018
Obseg dobave	Ohišje z izrezom in ojačitvijo za sistem nosilnih rok CP-L, Ø 130 mm Ključavnica z dvojnimi 3 mm vložkom Vrata s tesnilnim okvirjem Stranski ročaji in pokrovčki
Mere	Širina: 400 mm Višina: 400 mm Globina: 180 mm
IP razred zaščite po IEC 60 529	IP 55
Opomba	Priključek nosilne roke in tečaj vrat je mogoče zamenjati z vrtenjem ohišja
Osnovni material	Aluminium
Paketi	1 pc(s).
Neto teža	9,099 kg
Bruto teža	9,578 kg
Carinska tarifna številka	94032080
ECLASS 8.0	27180505