

**Rittal – The System.**

Faster – better – everywhere.



**CP 6660.010**

**Nosilni profil CP 40, nerjavno jeklo**

State: 26.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CP 6660.010 - Nosilni profil CP 40, nerjavno jeklo zaprto

Pritrditev na komponente z dvema vijakoma.

## Features

Št. Modela	CP 6660.010
Opis izdelka	Pritrditev na povezovalne elemente z dvema vpenjalnima vijakoma.
Material	Nerjavno jeklo 1.4301 (AISI 304)
Površinska obdelava	Brušeno, zrnatost 400
Obseg dobave	Nosilec
IP razred zaščite po IEC 60 529	IP 66 to IEC 60 529, 2014-09 IP X9 to IEC 60 529, 2014-09
Premer	48,3 mm
Dolžina	1.000 mm
Debelina materiala	3,6 mm
Paketi	1 pc(s).
Neto teža	3,7 kg
Bruto teža	3,9 kg
Carinska tarifna številka	73064020
ETIM 9	EC000882
ECLASS 8.0	27400556
Opis izdelka	CP Support section CP 40, solid, L: 1000 mm, stainless steel, 1.4301

## Approvals

Explanations

Manufacturer's declaration