

Rittal – The System.

Faster – better – everywhere.



CP 6663.400

Stenski/podnožni nosilec, vrtljiv, CP 40, nerjavno jeklo

State: 13.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6663.400 - Stenski/podnožni nosilec, vrtljiv, CP 40, nerjavno jeklo

For swivel mounting of the support arm system to vertical or horizontal surfaces.

Features

Št. Modela	CP 6663.400
Zasnova	Spredaj, luknja Ø 9 mm
Material	Nerjavno jeklo 1.4305 (AISI 303)
IP razred zaščite po IEC 60 529	IP 66 to IEC 60 529, 2014-09 IP X9 to IEC 60 529, 2014-09
Vrtenje/nagibanje	Yes
Rotation angle/swivel area	Približno 350°, pritrnitev z rebrastimi vijaki
Paketi	1 pc(s).
Neto teža	4,292 kg
Bruto teža	4,68 kg
Carinska tarifna številka	83024900
ETIM 9	EC000882
ECLASS 8.0	27400556
Opis izdelka	CP Wall/base mounting bracket, swivel, CP 40, front mounting, stainless steel, 1.4305

Approvals

Explanations

Manufacturer's declaration