

**Rittal – The System.**

Faster – better – everywhere.



**CP 6663.500**

**Stenski/podnožni nosilec, vrtljiv, CP 40, nerjavno jeklo**

State: 13.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CP 6663.500 - Stenski/podnožni nosilec, vrtljiv, CP 40, nerjavno jeklo

For swivel mounting of the support arm system to vertical or horizontal surfaces.

## Features

Št. Modela	CP 6663.500
Zasnova	Zadaj, navoj M8
Material	Nerjavno jeklo 1.4305 (AISI 303)
IP razred zaščite po IEC 60 529	IP 66 to IEC 60 529, 2014-09 IP X9 to IEC 60 529, 2014-09
Vrtenje/nagibanje	Yes
Rotation angle/swivel area	Približno 350°, pritrditev z rebrastimi vijaki
Paketi	1 pc(s).
Neto teža	3,657 kg
Bruto teža	3,98 kg
Carinska tarifna številka	83024900
ETIM 9	EC000882
ECLASS 8.0	27400556
Opis izdelka	CP Wall/base mounting bracket, swivel, CP 40, rear mounting, stainless steel, 1.4305

## Approvals

Explanations

Manufacturer's declaration