

Rittal – The System.

Faster – better – everywhere.



CP 6680.000 Premium Panel

State: 21.6.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6680.000 - Premium Panel Stainless steel

Premium Panel made of stainless steel 1.4301 (AISI 304), resistant to high-pressure cleaning.



Features

Model No.	CP 6680.000
Design	With keyboard housing
Benefits	Resistant to high-pressure cleaning: The seal lies between two surfaces and is optimally compressed by the screw fastening. Suitable for clean room use: Screw fastening to comply with high standards in the food industry. With plastic stoppers on the inside or hex screws on the outside.
Technical specifications	Keyboard housing is designed to fit mounting panel WxH: 482.6 mm (19") x 177 mm (4 U)
Material	Stainless steel 1.4301 (AISI 304)
Surface finish	Brushed, grain 400
Dimensions	Width: 530 mm
IP protection category to IEC 60529	IP 66 IP X9
To fit support arm connection	Top
Cleanroom class	Air purity class 1 to DIN EN ISO 14 644-1
Basic material	Stainless steel 1.4301 (AISI 304)
Note on Model No.	Extended delivery times.

Features

Packs of	1 pc(s).
Net weight	16.62
Gross weight	17.5
Customs tariff number	94039910
EAN	4028177305663
ETIM 9	EC002504
ECLASS 8.0	27180505