

# Rittal – The System.

Faster – better – everywhere.



## CP 6681.000 Premium Panel

State: 18.4.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CP 6681.000 - Premium Panel Stainless steel

Premium Panel made of stainless steel 1.4301 (AISI 304), resistant to high-pressure cleaning.



## Features

Model No.	CP 6681.000
Design	With support arm connection CP 40, stainless steel
Benefits	Resistant to high-pressure cleaning: The seal lies between two surfaces and is optimally compressed by the screw fastening. Suitable for clean room use: Screw fastening to comply with high standards in the food industry. With plastic stoppers on the inside or hex screws on the outside.
Material	Stainless steel 1.4301 (AISI 304)
Surface finish	Brushed, grain 400
Dimensions	Width: 530 mm Height: 360 mm Depth: 120 mm
IP protection category to IEC 60529	IP 66 IP X9
To fit support arm connection	Top or bottom (by rotating the enclosure)
Cleanroom class	Air purity class 1 to DIN EN ISO 14 644-1
Basic material	Stainless steel 1.4301 (AISI 304)
Packs of	1 pc(s).

# Features

---

Net weight	8,835 kg
Gross weight	9,3 kg
Customs tariff number	94039910
ETIM 9	EC002504
ECLASS 8.0	27180505
Product description	CP Premium Panel IP 69K, WHD: 530x360x120 mm, Stainless steel 1.4301, To fit panels WH 482.6x310 mm, Installation depth 115 mm

# Approvals

---

Explanations	Declaration of conformity Declaration of conformity UK PCF-declaration
--------------	--