

Rittal – The System.

Faster – better – everywhere.



TP 6722.500

Konzole za 3-delno montažo

State: 14.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TP 6722.500 - Konzole za 3-delno montažo

Štiri širine ponujajo odlične predpogoje za individualen nadzor in tridelno konfiguracijo sistema TopConsole.

Features

Št. Modela	TP 6722.500
Material	Ohišje: jeklena pločevina 1,5 mm Pokrov vrat in konzole: jeklena pločevina, 2,0 mm, penasto PU tesnilo po celotnem obodu
Površinska obdelava	Temeljni premaz, prašno barvana zunanost, teksturirana barva
Barva	RAL 7035
Obseg dobave	Ohišje Pokrov s tečaji spodaj, vključno z držalom pokrova Odprto podnožje za individualen vhod kablov
IK koda	IK08
Osnovni material	Sheet steel
Mere	Širina: 1.200 mm Višina: 720 mm Globina: 240 mm
IP razred zaščite po IEC 60 529	IP 55
Protection category NEMA	NEMA 12
Paketi	1 pc(s).
Neto teža	33,25 kg
Bruto teža	35 kg
Carinska tarifna številka	94032080
ETIM 9	EC000784
ECLASS 8.0	27180504
Opis izdelka	TP TopConsole system, console for 3-part assembly, WHD 1200x720 mm, sheet steel

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK
