

**Rittal – The System.**

Faster – better – everywhere.



# TP 6742.500

## Enodelne konzole TP

State: 21.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TP 6742.500 - Enodelne konzole TP

One-piece consoles TP, ready-to-use component with high protection category IP 55 in four different widths. Tool-free assembly of the cover with a lid stay. Compatibility with TS8 system accessories, such as base/plinths and cable entry grommets.

## Features

Št. Modela	TP 6742.500
Material	Ohišje: jeklena pločevina 1,5 mm Pokrov vrat in konzole: jeklena pločevina, 2,0 mm, penasto PU tesnilo po celotnem obodu Montažna plošča: jeklena pločevina, 3,0 mm
Površinska obdelava	Ohišje, pokrov in vrata: temeljni premaz, prašno barvana zunanost, teksturirana barva Montažna plošča: pocinkana
Barva	RAL 7035
Obseg dobave	Ohišje, zaprta zadnja stran in stranice Vrata ali dvojna vrata spredaj, z zaklepom Montažna plošča Pokrov s tečaji na zadnji strani, 2 držala za vrata s samodejnim zaklepanjem. Samodejno odklepanje na levi, ročno odklepanje na desni Odprto podnožje za individualen vhod kablov
Mere	Širina: 1.200 mm Višina: 973 mm
Mere montažne plošče (Š x V)	1.130 mm x 900 mm
Globina (zgoraj)	500 mm
Globina (spodaj)	400 mm
Število vrat	2
IK koda	IK08
Opomba za model št.	Pri različici z dvema vrati je osnovna odprtina razdeljena na dva dela, zato sta potrebna dva paketa tesnilnih plošč.
IP razred zaščite po IEC 60 529	IP 55

## Features

Protection category NEMA	NEMA 12
Osnovni material	Sheet steel
Mere	Širina: 1.200 mm Višina: 973 mm Globina (zgoraj): 500 mm Globina (spodaj): 400 mm
Paketi	1 pc(s).
Neto teža	85,5 kg
Bruto teža	90 kg
Carinska tarifna številka	94032080
ECLASS 8.0	27180504
Opis izdelka	TP one-piece console, WHD1: 1200x960x400/D2: 500 mm, sheet steel

## Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity