

Rittal – The System.

Faster – better – everywhere.



TP 6746.500 Enodelne konzole TP

State: 7.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TP 6746.500 - Enodelne konzole TP

One-piece consoles TP, ready-to-use component with high protection category IP 55 in four different widths. Tool-free assembly of the cover with a lid stay. Compatibility with TS8 system accessories, such as base/plinths and cable entry grommets.

Features

Št. Modela	TP 6746.500
Material	Ohišje: jeklena pločevina 1,5 mm Pokrov vrat in konzole: jeklena pločevina, 2,0 mm, penasto PU tesnilo po celotnem obodu Montažna plošča: jeklena pločevina, 3,0 mm
Površinska obdelava	Ohišje, pokrov in vrata: temeljni premaz, prašno barvana zunanost, teksturirana barva Montažna plošča: pocinkana
Barva	RAL 7035
Obseg dobave	Ohišje, zaprta zadnja stran in stranice Vrata ali dvojna vrata spredaj, z zaklepom Montažna plošča Pokrov s tečaji na zadnji strani, 2 držala za vrata s samodejnim zaklepanjem. Samodejno odklepanje na levi, ročno odklepanje na desni Odprto podnožje za individualen vhod kablov
Mere	Širina: 600 mm Višina: 973 mm
Mere montažne plošče (Š x V)	530 mm x 900 mm
Globina (zgoraj)	500 mm
Globina (spodaj)	400 mm
Število vrat	1
IK koda	IK08
Opomba za model št.	Pri različici z dvema vrata je osnovna odprtina razdeljena na dva dela, zato sta potrebna dva paketa tesnilnih plošč.
IP razred zaščite po IEC 60 529	IP 55

Features

Protection category NEMA	NEMA 12
Osnovni material	Sheet steel
Mere	Širina: 600 mm Višina: 973 mm Globina (zgoraj): 500 mm Globina (spodaj): 400 mm
Paketi	1 pc(s).
Carinska tarifna številka	94032080
ECLASS 8.0	27180504
Opis izdelka	TP one-piece console, WHD1: 600x960x400/D2: 500 mm, sheet steel

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity