

Rittal – The System.

Faster – better – everywhere.



TE 7000.672 Transport castors

State: 6.8.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TE 7000.672 - Transport castors for FlatBox

Transport castors, for FlatBox.

Features

| | |
|-----------------------|--|
| Model No. | TE 7000.672 |
| Product description | The castors may be screw-fastened in the corner areas within the base frame in place of the levelling feet. Ground clearance: 58 mm, mounting thread M10 x 20. |
| Supply includes | Assembly parts |
| Load capacity | 3.000 N |
| Packs of | 4 pc(s). |
| Net weight | 0.8 |
| Gross weight | 0.938 |
| Customs tariff number | 83024900 |
| EAN | 4028177437340 |
| E-Number Sweden | E7239804 |
| ETIM 9 | EC000721 |
| ECLASS 8.0 | 27182003 |

Tender text

TE transport castors

For easy transportation between sites. The castors can be screwed into the corners of the base frame in addition to the levelling feet.

Load capacity: 300 kg static

Height: 58.5 mm