

Rittal – The System.

Faster – better – everywhere.



DK 7010.150

Senzorji

State: 16.7.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7010.150 - Senzorji for CMC III, PDU, LCP, IoT interface

The differential pressure sensor measures the air pressure at two points and displays the pressure difference between them.

Features

Št. Modela	DK 7010.150
Zasnova	Differential pressure sensor
Prednosti	Hitra povezava in samodejno zaznavanje s funkcijo plug & play Napajanje se omogoči s povezavo z vmesnikom CAN-BUS.
Aplikacije	Nadzor ohišij v IT, industriji in upravljanju objektov Nadzor ohišij, prostorov in zabojnikov v IT okolju
Način delovanja	Settings can be made via the CMC III processing unit, PDU or IoT interface The differential pressure sensor measures the air pressure at two points in the room and displays the pressure difference between them. Dve točki v prostoru sta določeni s tanko cevjo, priključeno na senzor.
Material	Plastika
Površinska obdelava	Spredaj: gladko Ohišje: teksturirano
Barva	RAL 9005
Obseg dobave	Senzor Montažna plošča Sestavni deli
Povezava s CAN vodilom	Direct
Vmesniki	2 x RJ45 CAN bus
Mere	Širina: 110 mm Višina: 30 mm Globina: 40 mm
Delovno temperaturno območje	0 °C...45 °C

Features

Vlažnost okolice (brez kondenzacije)	0...95 %
Paketi	1 pc(s).
Neto teža	0,333 kg
Bruto teža	0,383 kg
Carinska tarifna številka	85319000
Opis izdelka	DK Differential pressure sensor, for bayed enclosure suites, connection via CAN bus interface, WxHxD: 110x30x40 mm, RAL 9005

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity