

Rittal – The System.

Faster – better – everywhere.



DK 7010.190

Senzorji

State: 14.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7010.190 - Senzorji for CMC III, PDU, LCP, IoT interface

Universal sensor with two digital inputs and one analogue input, which can be configured as required for the application in question.

Features

Št. Modela	DK 7010.190
Zasnova	Universal sensor
Prednosti	Hitra povezava in samodejno zaznavanje s funkcijo plug & play Napajanje se omogoči s povezavo z vmesnikom CAN-BUS.
Aplikacije	Nadzor ohišij v IT, industriji in upravljanju objektov Nadzor ohišij, prostorov in zabožnikov v IT okolju
Način delovanja	Settings can be made via the CMC III processing unit, PDU or IoT interface Senzor ima dva digitalna vhoda in en analogni vhod, ki jih je mogoče konfigurirati glede na potrebe posamezne aplikacije. Digitalni vhodi se lahko konfigurirajo kot 2x brezpotencialna nadzorna kontakta, 2x vhoda S0 bus (merilniki energije) ali 1x vmesnik Wiegand (zunanji dostopni sistemi). Analogni vhod se lahko uporablja kot vmesnik 4–20 mA.
Material	Plastika
Površinska obdelava	Spredaj: gladko Ohišje: teksturirano
Barva	RAL 9005
Obseg dobave	Univerzalni senzor
Povezava s CAN vodilom	Direct
Vmesniki	2 x RJ45 CAN bus analog, 4 – 20 mA 2 digital inputs/S0 bus/Wiegand
Mere	Širina: 110 mm Višina: 30 mm Globina: 40 mm
Delovno temperaturno območje	0 °C...45 °C

Features

Vlažnost okolice (brez kondenzacije)	0...95 %
Paketi	1 pc(s).
Neto teža	0,127 kg
Bruto teža	0,157 kg
Carinska tarifna številka	85319000
Opis izdelka	DK universal sensor, for bayed enclosure suites, connection via CAN bus interface, WHD: 110x30x40 mm, RAL 9005

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity