


# Rittal – The System.

Faster – better – everywhere.



## DK 7063.883

## Slide rail, 1 U, depth-variable

State: 13.12.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7063.883 - Slide rail, 1 U, depth-variable for server and network racks with two 482.6 mm (19") mounting levels and TE, L-shaped mounting angles

For TE, 482.6 mm (19") mounting frame, L-shaped mounting angles, pull-out.

## Features

Model No.	DK 7063.883
Product description	The slide rail is pulled out to the required length and secured between the front and rear mounting level. Rear location lugs and front screw-fastening enable convenient one-man assembly. The mounting component to be integrated is inserted horizontally onto the slide rail and optionally secured to the mounting level via its attachment slots.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Note	The super-slimline design of the slide rail allows it to be used in most integration cases for 482.6 mm (19") mounting components. Because it is secured to the standardised mounting level, it is manufacturer-independent. The slide rail slightly reduces the installation space below the slide rail so that the U below it is only available for limited use.
Load capacity (static)	80 kg
Contact surface	Width: 50 mm
Length	590: 930 mm
Packs of	2 pc(s).
Net weight	3.25
Customs tariff number	73269098
EAN	4028177517783

# Features

---

ECLASS 8.0

27189261

## Tender text

Slide rail, depth-adjustable,  
590 . 930 mm extension, capacity 80 kg

Slide rail, depth-adjustable, 590 . 930 mm extension.  
For direct attachment to the 482.6 mm (19.) system  
punchings.

2 slide rails, including assembly parts

Load capacity: 80 kg, static.

Material: sheet steel, zinc-plated, passivated