

Rittal – The System.

Faster – better – everywhere.



IT 7100.110 OCP ORV3 stojalo

State: 23.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



IT 7100.110 - OCP ORV3 stojalo

Open. Efficient. Scalable. Your IT infrastructure from Rittal with OCP ORV3, without busbar. The Open Compute Project (OCP) brings together leading companies with the goal of making open IT infrastructures more efficient, scalable and sustainable. Rittal is supporting this vision with its OCP-compliant Open Rack Version 3 (ORV3), which is now also available without an integral busbar.



Features

Št. Modela	IT 7100.110
Zasnova	Odprt okvir without busbar
Prednosti	Modularni sistem za individualne možnosti razširitve Flexible busbar selection, to suit the rack power density Can be retrofitted without replacing the entire system Modular configuration for AI and HPC applications Hot-pluggable components in the rack simplify maintenance work May be supplemented with a suitable direct liquid cooling solution Quick integration thanks to integral castor modules, air baffle plates and levelling feet Our range of accessories includes IT and power rails, 482.6 mm (19") adaptors, doors and side panels
Material	Jeklena pločevina
Površinska obdelava	Temeljni premaz, prašno barvana zunanost
Barva	RAL 9005

Features

Obseg dobave	OCP ORV3 stojalo 2 podporna droga, predsestavljena Prednameščena kolesa za težke obremenitve Nivelirne noge, predsestavljene Povezovalno tesnilo
Mere	Širina: 600 mm Višina: 2.286 mm Globina: 1.068 mm
Enote	44 OU
Nosilnost	14.000 N
Osnovni material	Sheet steel
Paketi	1 pc(s).
Carinska tarifna številka	94032080
ETIM 8	EC002499
ECLASS 8.0	27180207
Opis izdelka	OCP ORV3 rack without busbar, 44 OU, WHD: 600 x 2286 x 1068 mm, RAL 9005