

# Rittal – The System.

Faster – better – everywhere.



## DK 7111.300

# Zaskočna napeljava kablov

State: 27.5.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7111.300 - Zaskočna napeljava kablov

Za hitro namestitvev brez orodja v dveh različicah: montaža s klikom in montaža z zasukom.



## Features

Št. Modela	DK 7111.300
Zasnova	za pritisno montažo
Opis izdelka	Univerzalno vodilo za kabel za hitro montažo brez orodja v sistemsko odprtino s premerom 6,2 mm. Sponko za kabel je mogoče enostavno odpreti za vstavitvev kabla s samodejnim zapiranjem.
Prednosti	Premer objemke za kabelsko napeljavo se lahko prilagodi preseku napeljanega kabla
Material	Poliamid 6.6, samougasljiv po UL 94-V2
Barva	Naravno
Kabelske uvodnice	Min. premer kabla: 14 mm Maks. premer kabla: 19 mm
For system punchings with Ø	6,2 mm
Min. premer kabla	14 mm
Maks. premer kabla	19 mm

# Features

Paketi	10 pc(s).
Neto teža	0,03 kg
Bruto teža	0,043 kg
Carinska tarifna številka	39269097
ETIM 9	EC002625
ECLASS 8.0	27189234
Opis izdelka	DK snap-in cable routing for snap-mounting, for fast, tool-free assembly, for max. Ø 19 mm, polyamide, natural