

Rittal – The System.

Faster – better – everywhere.



DK 7241.024 Patch panels

State: 13.4.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7241.024 - Patch panels for fibre-optic splicing box, depth-variable, and fibre-optic breakout box, 1 U

With cut-outs for population with fibre-optic couplings.

Features

| | |
|-------------------------------|--|
| Model No. | DK 7241.024 |
| Product description | With cut-outs for population with fibre-optic couplings. |
| Applications | for fibre-optic splicing box, depth-variable, and fibre-optic breakout box, 1 U |
| Material | Sheet steel |
| Colour | RAL 7035 |
| Number of locations | 24 |
| for fibre-optic coupling | E-2000 E-2000 duplex SC LC duplex |
| Note on Model No. | For E-2000 duplex only half of the locations are available. |
| Units | 1 U |
| Packs of | 1 pc(s). |
| Net weight | 0,2 kg |
| Gross weight | 0,263 kg |
| PCF per pack (cradle-to-gate) | 1 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94039910 |
| ETIM 9 | EC001129 |
| ECLASS 8.0 | 19170113 |
| Product description | DK Patch panel |

Tender text

Patch panel, 1 U, for fibre-opt. splic. box
24-port E-2000/SC

For coupling: E-2000, E-2000 duplex (only half of the installation slots are available with E-2000 duplex versions) or SC. Number of installation slots:
24 x 1 U

Fixing measurement: 400 mm

Material: Sheet steel, spray finished in RAL 7035