Rittal - The System.

Faster – better – everywhere.





DK 7282.035 Drawer

State: 7.12.2025 (Source: rittal.com/si-sl)



DK 7282.035 - Drawer for one 482.6 mm (19") mounting level

For front attachment to mounting angles, 482.6 mm (19"). With cover and telescopic slides to accommodate assignment lists, operating manuals and small parts.



Features

For front attachment to mounting angles, 482.6 mm (19"). With cover and telescopic slides to accommodate assignment lists, operating manuals and small parts. The small version of the 2 U
variant is also suitable for mounting inside a swing frame.
Sheet steel
RAL 7035
Fully assembled Security lock 12321
419 mm
411 mm
1 pc(s).
6.435
6.82
25.8 kg CO2 eq (Cat B)
Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared

© Rittal 2025

Features

Customs tariff number	94039910
EAN	4028177165953
ETIM 9	EC002620
ECLASS 8.0	27189261

Tender text

Keyboard drawer, 482.6 mm (19 inch), 2 U

Material: Sheet steel, spray finished in RAL 7035

Installation depth: 427 mm

© Rittal 2025 3