Rittal – The System.

Faster – better – everywhere.





DK 7492.070 Slide rail, heavy-duty

State: 7.11.2025 (Source: rittal.com/si-sl)



DK 7492.070 - Slide rail, heavy-duty for TS network enclosures with two mounting levels

For TS network enclosures with two 482.6 mm (19") mounting levels, to support heavy installed equipment.

Features

Model No.	DK 7492.070
Design	For static installation between two 482.6 mm (19") mounting levels.
Product description	To support heavy installed equipment. The slide rails are simply located into the cranked mounting angles and secured with screws. The combined use with additional depth stays or, in case of 80 mm wide enclosures, with the additional fastening attachment counteracts possible bending of the mounting angles in case of unevenly distributed loads.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Distance between mounting levels	698 mm
Load capacity	80 kg, static load
Note	Not suitable in combination with 482.6 mm (19") mounting frame Please select slide rails according to the relevant 482.6 mm (19") distance between levels. If combining with L-shaped mounting angles, a mounting adaptor for L-shaped mounting angles must be used.
Contact surface	Width: 55 mm Depth: 661 mm
Packs of	2 pc(s).
Net weight	1.52
Gross weight	1.719
Customs tariff number	73269098

© Rittal 2025 2

Features

EAN	4028177541382	
ETIM 9	EC002620	
ECLASS 8.0	27189261	

© Rittal 2025 3