

Rittal – The System.

Faster – better – everywhere.



CP 7495.000 Twin castors

State: 22.8.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 7495.000 - Twin castors

For mobile use, for mounting directly on the enclosure.

Features

Model No.	CP 7495.000
Product description	For mobile use, for mounting directly on the enclosure.
Colour	Black
Supply includes	4 twin castors, 2 x with, 2 x without locks Assembly parts
Note on Model No.	A base/plinth adaptor is required for mounting on the VX base/ plinth A base/plinth adaptor is required for mounting on the TS base/ plinth.
To fit	Enclosure type: VX Enclosure type: VX IT Enclosure type: VX SE Enclosure type: PC Enclosure type: TP pedestals Enclosure type: IW Enclosure type: Data Rack Enclosure type: Chiller
Clearance floor	125 mm
Max. load capacity (static) per component	1.200 N
Dimensions	Thread: M12 x 20
Packs of	4 pc(s).
Net weight	1.76
Gross weight	1.98
Customs tariff number	83024900
EAN	4028177131200
E-Number Sweden	E7239729

Features

ETIM 9	EC002621
ECLASS 8.0	27189262

Tender text

Twin castors

Mounting on the frame

Suitable for:

VX, VX IT, VX SE, PC cabinet system, top console lower parts, Industrial workstation (IW), Data rack, Chiller

For mounting on the VX base, a base adapter for double twin castors is required (8100.770 or 8100.771)

Fitted to VX, AX, KX, TS, PS, ES & AP frames, PC enclosures,

Material: RAL 9005 (black)

Dimensions (W x H x D): 0 mm x 125 mm x 0 mm