

# Rittal – The System.

Faster – better – everywhere.



## DK 7645.000

## Stenska AE ohišja

State: 21.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7645.000 - Stenska AE ohišja z montažnimi kotniki 482,6 mm (19"), spremenljiva globina

Wall-mounted enclosure for small networks with fixed 482.6 mm (19") mounting level and gland plate with brush strip for cable entry at the bottom. Protection category IP 55.

## Features

Št. Modela	DK 7645.000
Material	Ohišje: jeklena pločevina
Površinska obdelava	Ohišje: prašno barvano Montažni kotni nosilci: pocinkano
Barva	RAL 7035
Obseg dobave	Ohišje z vrati na tečajih Vrata s tečaji na desni, možnost menjave na levo Ključavnica z dvojnimi 3 mm vložki Plošča z uvodnicami s krtačnim trakom za vhod kablov v dno ohišja Montažni kotniki, 482,6 mm (19"), popolnoma nastavljivi po globini C profil za vpenjanje kablov na zadnji plošči Kovinski nosilec za opcijsko namestitev ozemljitvene tirnice ali 482,6 mm (19") vtičnic
Enote	16 U
Mere	Širina: 600 mm Višina: 760 mm Globina: 350 mm
Globina namestitve	310 mm
Višina vgradnje komponent	16 U
Položaj tečajev vrat	right, may be swapped to the left
Število ključavnic	2
Osnovni material	Sheet steel
Razred zaščite po IEC 60 529	Up to IP 66 (depending on the selected gland pate)

# Features

---

Plošča za kableske uvodnice	Velikost: 5 Količina: 1
Paketi	1 pc(s).
Neto teža	29,7 kg
Bruto teža	30,1 kg
Carinska tarifna številka	94032080
ETIM 9	EC002500
ECLASS 8.0	27180208
Opis izdelka	DK Wall-mounted enclosures AE, WHD:600x760x350 mm, 16 U, AE 1376

# Approvals

---

Approvals	TÜV VDE
-----------	------------