

Rittal – The System.

Faster – better – everywhere.



DK 7824.188 Side panel, lockable

State: 2.2.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7824.188 - Side panel, lockable for TS, TS IT

Side panel, lockable, sheet steel, for TS.



Features

| | |
|-----------------------|---|
| Model No. | DK 7824.188 |
| Product description | Simply locate from above. Lock with security lock no. 3524 E. Earthing bolt with contact track. |
| Material | Sheet steel |
| Surface finish | Spray-finished |
| Colour | RAL 7035 |
| Supply includes | 2 side panels each with 4 security locks no. 3524 E |
| To fit | Enclosure type: TS TS IT Height: 1,800 mm Depth: 800 mm |
| Basic material | Sheet steel |
| Packs of | 2 pc(s). |
| Net weight | 34.4 |
| Gross weight | 35.8 |
| Customs tariff number | 94039910 |
| EAN | 4028177232037 |
| E-Number Sweden | E7282526 |
| ETIM 9 | EC002524 |

Features

ECLASS 8.0

27182101

Tender text

Colour

RAL 7035

Material

Sheet steel, spray-finished

Supply includes

2 side panels with toggle locks

Dimensions mm W x H x D

Height 1800 mm, depth 800 mm