

Rittal – The System.

Faster – better – everywhere.



DK 7826.786

Roof plate, vented

State: 22.7.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7826.786 - Roof plate, vented for TS, TS IT

In exchange for the standard roof, with and without cable entry.



Features

| | |
|-----------------------|--|
| Model No. | DK 7826.786 |
| Design | One-piece without cable entry |
| Product description | In exchange for the standard roof. 72 mm high roof plate, all-round vent slots, clamp strip for cable entry. The two-piece design with cable entry allows convenient retrofitting. |
| Material | Sheet steel |
| Colour | RAL 7035 |
| To fit | Enclosure type: TS TS IT Width: 800 mm Depth: 600 mm |
| Packs of | 1 pc(s). |
| Net weight | 6.904 |
| Gross weight | 7.267 |
| Customs tariff number | 73269098 |
| EAN | 4028177345621 |
| ETIM 9 | EC000744 |
| ECLASS 8.0 | 27182405 |

Tender text

DK-TS vented roof plate, W x D = 800 x 600 mm

Material: Sheet steel, spray finished in RAL 7035

Dimensions (W x H x D): 800 mm x 0 mm x 600 mm