

Rittal – The System.

Faster – better – everywhere.



DK 7827.221

Mounting angles, 482.6 mm (19")

State: 16.4.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7827.221 - Mounting angles, 482.6 mm (19") for TS

L-shaped mounting angles, also for accommodating server system installation kits.

Features

| | |
|--------------------------|---|
| Model No. | DK 7827.221 |
| Design | L-shaped mounting angle |
| Benefits | Integral U markings in the front facilitate systematic assembly within the 482.6 mm (19") attachment level. L-shaped mounting angles accommodate the installation kits of server systems Suitable for 482.6 mm (19") partial installation |
| Technical specifications | Integral 482.6 mm (19") punchings (EIA standard) Side round and square punchings Clear chromated for conductive connection of the 482.6 mm (19") installed equipment. |
| Material | Sheet steel, 2 mm |
| Supply includes | Assembly parts |
| Units | 47 U |
| Note | Please select slide rails according to the relevant 482.6 mm (19") distance between levels. If combining with L-shaped mounting angles, a mounting adaptor for L-shaped mounting angles must be used. |
| To fit | Enclosure type: TS Height: 2,200 mm |
| Packs of | 2 pc(s). |
| Net weight | 4,958 kg |
| Gross weight | 5,218 kg |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |

Features

Product description

DK-TS Mounting angles, 482.6 mm (19"), L-shaped mounting angle,
For H: 2200 mm, 47 U

Tender text

DK-TS mounting angles, L-shaped, 47 U

Technical specifications: 2 mm sheet steel, with integrated 482.6 mm (19") punchings as well as 25 mm DIN pitch pattern round and square holes. Zinc-plated, passivated for conductive connection to the installed 482.6 mm (19") equipment.

Material: Sheet steel, zinc-plated, passivated