

**Rittal – The System.**

Faster – better – everywhere.



**DK 7955.134**

**Mednarodna PDU enota, osnovna različica**

State: 21.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7955.134 - Mednarodna PDU enota, osnovna različica

IT rack power distribution in a range of different variants. Input with CEE connector (16 A/32 A) and C13 and C19 outputs. Distribution output from 3.7 kW to 22 kW.

## Features

Št. Modela	DK 7955.134
Zasnova	PDU Basic
Material	Aluminijast profil, črno eloksirano
Mere	Širina: 44 mm Globina: 62 mm Dolžina: 1.710 mm
Število vtičnic in tip	36 x C13 / 6 x C19
Vtičnice	36 x IEC 320 socket C13 6 x IEC 320 socket C19
Nazivni tok (maks.)	32 A
Dovodni vodi	Količina: 1 Faze na dovod: 3~
Dolžina priključnega kabla	3 m
Vrsta električne povezave	CEE
Number RJ45 ports for sensor units max	6
Direktive	Direktiva o elektromagnetni združljivosti 2014/30/EU Direktiva o nizki napetosti 2014/35/EU
Standardi	EN 60950-1
Delovno temperaturno območje	0 °C...45 °C
Vlažnost okolice (brez kondenzacije)	10...95 %
Temperaturno območje shranjevanja	-25 °C...70 °C

# Features

Primerno za	Vrsta ohišja: TS IT: ≥ 2.000 mm
Paketi	1 pc(s).
ETIM 9	EC002762
ECLASS 8.0	27142604
Opis izdelka	DK PDU international, basic version, Compact basic power distributor, WLD: 44x1710x62 mm, 36xC13, 6xC19, black, CEE, 3~, 32 A