### Rittal – The System.

Faster – better – everywhere.





## TS 8601.060

# Base/plinth trim panels, side, 100 mm

State: 26.10.2025 (Source: rittal.com/si-sl)



## TS 8601.060 - Base/plinth trim panels, side, 100 mm for base/plinth components front and rear

For mounting between the base/plinth components. At 200 mm height, two 100 mm base/plinth trims may be used. Base/plinth trims may be installed rotated through 90° in order to stabilise bayed base/plinth components.

#### **Features**

Model No.	TS 8601.060
Product description	For mounting between the base/plinth components. At 200 mm height, two 100 mm base/plinth trim panels may be used.
Material	Sheet steel
Surface finish	Spray-finished
Colour	RAL 7022
Supply includes	2 base/plinth trim panels Assembly parts
Assembly instruction	Base/plinth trim panels, side, 100 mm, may be installed rotated through 90° to stabilise bayed base/plinth components. The base/plinth baying bracket is required for this purpose
Dimensions	Height: 100 mm
To fit	Enclosure type: TS: = 600 mm  Enclosure type: SE  Enclosure type: CM  Enclosure type: TP  Enclosure type: PC  Enclosure type: IW  Enclosure type: TS IT
Packs of	2 pc(s).
Net weight	1.798
Gross weight	1.997
Customs tariff number	94039910

© Rittal 2025

### **Features**

EAN	4028177208650
ECLASS 8.0	27182003

© Rittal 2025 3