

Rittal – The System.

Faster – better – everywhere.



TS 8606.300 TS 8 corner enclosures

State: 2019 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8606.300 - TS 8 corner enclosures

For corner baying of TS 8 enclosures, also with different depths.

Features

| | |
|-----------------------|--|
| Model No. | TS 8606.300 |
| Product description | The corner enclosure and the supplied components will accommodate the various baying options of the TS 8 frame on all outer surfaces. Fitted with a rear panel and an asymmetrical side panel, the corner enclosure also permits the option of baying in both the width and depth. The gland plates are aligned parallel to the rear panel. In TS 8 enclosures with a square footprint, the gland plates may also be rotated through 90°. The baying system is identical to all other TS 8 enclosures. |
| Material | Sheet steel, 1.5 mm |
| Surface finish | Enclosure frame, roof, rear wall and side panel: Dipcoat-primed, powder-coated on the outside, textured paint Gland plates: Zinc-plated |
| Colour | RAL 7035 |
| Supply includes | Enclosure frame Roof Rear wall (on the longest side) Side panel, asymmetrical Gland plates (divided in a longitudinal direction) |
| Note on Model No. | Extended delivery times. |
| Dimensions | Width: 600 mm Height: 2,000 mm Depth: 600 mm |
| Packs of | 1 pc(s). |
| Net weight | 100 |
| Gross weight | 104 |
| Customs tariff number | 94032080 |
| EAN | 4028177251540 |

Features

| | |
|------------|----------|
| ECLASS 8.0 | 27180101 |
|------------|----------|

Approvals

| | |
|--------------|---------------------------|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity |
