

Rittal – The System.

Faster – better – everywhere.



TS 8610.800 Steklena vrata

State: 22.5.2026 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8610.800 - Steklena vrata za TS 8

Glazed doors for TS 8 instead of a sheet steel door or rear panel.



Features

Št. Modela	TS 8610.800
Material	Okvir: ekstrudiran aluminijast profil Kotni elementi: tlačno liti cink Nadzorno okno: enoslojno varnostno steklo, 3 mm
Površinska obdelava	Prašno barvano
Barva	RAL 7035 Nadzorno okno (potiskana notranjost): RAL 7015
Obseg dobave	Okvir vrat z varnostnim steklom Ključavnica z dvojnimi vložki 180° tečaji (4) Vidna površina: Š – 140 mm, V – 160 mm.
Vidno območje	Širina nadzornega okna: 640 mm Višina nadzornega okna: 1.840 mm
Višina nadzornega okna	1.840 mm
IP razred zaščite po IEC 60 529	IP 55

Features

Primerno za	Vrsta ohišja: DK-TS TS 8 SE Širina: = 800 mm Višina: = 2.000 mm
-------------	---

Paketi	1 pc(s).
--------	----------

Neto teža	33,25 kg
-----------	----------

Bruto teža	35 kg
------------	-------

Carinska tarifna številka	76101000
---------------------------	----------

ECLASS 8.0	27182204
------------	----------
