

Rittal – The System.

Faster – better – everywhere.



TS 8612.780

TS punched rail 25 x 38 mm

State: 16.5.2025 (Source: [rittal.com/si-sl](https://www.rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8612.780 - TS punched rail 25 x 38 mm

For heavy installations, with attachment holes. Installation options on the vertical TS enclosure section.



Features

Model No.	TS 8612.780
Product description	For heavy installations, with attachment holes.
Material	Sheet steel, 3.0 mm
Surface finish	Zinc-plated
Supply includes	Assembly screws
Installation options	On the vertical TS, VX SE enclosure section With 9 mm round holes all round on a 25 mm pitch pattern For the external mounting angle of support rails, system support rails, C rails 30/15, cable clamp rails (right angle section), own assemblies
Note	In conjunction with the snap-on nut, particularly well-suited for dynamic connections
To fit	To fit width/depth: 800 mm
Packs of	2 pc(s).
Net weight	2.488
Gross weight	2.687
Customs tariff number	73269098
EAN	4028177429154

Features

ETIM 9	EC002620
ECLASS 8.0	27189261