

Rittal – The System.

Faster – better – everywhere.



VX 8619.790

Izrezani profil z montažno prirobnico, 14 x 39 mm

State: 28.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8619.790 - Izrezani profil z montažno prirobnico, 14 x 39 mm za VX, VX SE, PC, IW, AX

Za pritrditev kablskih kanalov, nosilcev kablskih kanalov, opreme, nameščene na vratih itd.



Features

Št. Modela	VX 8619.790
Opis izdelka	Za pritrditev kablskih kanalov, nosilcev kablskih cevi, komponent za vrata itd.
Material	Jeklena pločevina
Površinska obdelava	Pocinkano
Obseg dobave	Sestavni deli
Distance between fixing points	635 mm
Možnosti namestitve AX	V ohišjih z višino 760 mm, skupaj s tirnico za notranjo montažo AX
Navodila za sestavljanje	Za vgradnjo v AX jeklena pločevina, samo v kombinaciji z letvijo za notranjo namestitev AX
Opomba	Za namestitev lastnih komponent na luknjani del z montažno prirobnico so potrebni kovinski vijaki ali samorezni vijaki M5
Primerno za	Vrsta ohišja: AX Suitable for width or height or depth: 760 mm
Paketi	4 pc(s).
Neto teža	1,2 kg

Features

Bruto teža	1,52 kg
PCF na paket (od zibelke do vrat)	9,9
Carinska tarifna številka	73269098
ETIM 9	EC002620
ECLASS 8.0	27189234
Opis izdelka	VX Punched section with mounting flange, 14 x 39 mm , for door width: 760 mm

Approvals

Explanations	PCF-declaration
--------------	-----------------