


Rittal – The System.

Faster – better – everywhere.



VX 8620.005

**Kotni element podnožja/podstavka
z obrobami podnožja/podstavka,
spredaj in zadaj, 100 mm**

State: 21.6.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8620.005 - Kotni element podnožja/podstavka z obrobami podnožja/podstavka, spredaj in zadaj, 100 mm za VX, VX IT, VX SE, TE, TS, TS IT, TP, PC, IW

Base/plinth corner pieces with moulded self-positioning to the bayed enclosure system, for use with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimum access to the screw-fastening point may be concealed with a corner and baying cover.

Features

Št. Modela	VX 8620.005
Material	Podnožje/vogalni kos podnožja: jeklena pločevina Obroba podnožja/podstavka spredaj/zadaj: jeklena pločevina Kotni in povezovalni pokrov: plastika
Barva	RAL 9005
Obseg dobave	4 vogalni elementi podnožja/podstavka, višina 100 mm 4 vogalni pokrovi 1 povezovalni pokrov 2 obrobi podnožja/podstavka, spredaj/zadaj, višina 100 mm Sestavni deli
Opomba	Stranske obrobe podnožja/podstavka zaokrožujejo podnožje/podstavke ali zagotavljajo dodatno stabilizacijo med podnožjem/podstavkom oziroma omogočajo notranjo konfiguracijo podnožja/podstavka
Mere	Višina: 100 mm
Primerno za	Vrsta ohišja: VX Širina: = 1.000 mm
Teža/pakiranje	5,7 kg
Paketi	2 pc(s).
Neto teža	5,5 kg
Carinska tarifna številka	94039910

Features

ECLASS 8.0

27182003

Opis izdelka

VX Base/plinth corner piece, with base/plinth trim panel, front and rear, H: 100 mm, for W: 1000 mm, sheet steel

Approvals

Approvals

UL + C-UL - FTTA