

Rittal – The System.

Faster – better – everywhere.



VX 8620.024

**Vogalni element podnožja/
podstavka z obrobami podnožja/
podstavka, spredaj in zadaj, 200
mm**



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDRICH LOH GROUP

VX 8620.024 - Vogalni element podnožja/podstavka z obrobami podnožja/podstavka, spredaj in zadaj, 200 mm za VX, VX IT, VX SE, TE, TS, TS IT, TP, PC, IW

Base/plinth corner pieces with moulded self-positioning to the bayed enclosure system, for use with or without trim panels depending on the application. Large openings in the base/plinth corner piece for optimum access to the screw-fastening point may be concealed with a corner and baying cover.

Features

Št. Modela	VX 8620.024
Material	Podnožje/vogalni kos podnožja: jeklena pločevina Obroba podnožja/podstavka spredaj/zadaj: jeklena pločevina Kotni in povezovalni pokrov: plastika
Barva	RAL 9005
Obseg dobave	4 vogalni elementi podnožja/podstavka, višina 200 mm 4 vogalni pokrovi 1 povezovalni pokrov 1 obroba podnožja/podstavka, spredaj/zadaj, višina 200 mm 2 obrobi podnožja/podstavka, spredaj/zadaj, višina 100 mm Sestavni deli
Opomba	Stranske obrobe podnožja/podstavka zaokrožujejo podnožje/ podstavek ali zagotavljajo dodatno stabilizacijo med podnožjem/ podstavkom oziroma omogočajo notranjo konfiguracijo podnožja/ podstavka
Mere	Višina: 200 mm
Primerno za	Vrsta ohišja: VX Širina: = 1.000 mm
Teža/pakiranje	9,98 kg
Paketi	2 pc(s).
Neto teža	9,78 kg
Carinska tarifna številka	94039910

Features

ECLASS 8.0

27182003

Opis izdelka

VX Base/plinth corner piece, with base/plinth trim panel, front and rear, H: 200 mm, for W: 1000 mm, sheet steel

Approvals

Approvals

UL + C-UL - FTTA