


Rittal – The System.

Faster – better – everywhere.



VX 8640.030

Obrobe podnožja/podstavka, stranske, 100 mm

State: 12.5.2026 (Source: rittal.com/si-sl)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8640.030 - Obrobe podnožja/podstavka, stranske, 100 mm za VX sistem podnožja/podstavka, jeklena pločevina

To finish off a base/plinth unit at the sides and for additional stability, or for the interior installation of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.

Features

Št. Modela	VX 8640.030
Material	Jeklena pločevina
Barva	RAL 9005
Obseg dobave	Sestavni deli
Mere	Višina: 100 mm
Primerno za	Globina: = 300 mm
Tipska ocena po UL 50E	Type 1, 12
Teža/pakiranje	0,614 kg
Paketi	2 pc(s).
Neto teža	0,6 kg
Bruto teža	0,614 kg
Carinska tarifna številka	94039910
ETIM 9	EC000721
ECLASS 8.0	27182003
Opis izdelka	VX Base/plinth trim panel, side, H: 100 mm, for D: 300 mm, sheet steel

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------