

**Rittal – The System.**

Faster – better – everywhere.



**VX 8640.044**

**Obrobe podnožja/podstavka,  
stranske, 200 mm**

State: 13.6.2026 (Source: [rittal.com/si-sl](http://rittal.com/si-sl))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8640.044 - Obrobe podnožja/podstavka, stranske, 200 mm za VX sistem podnožja/podstavka, jeklena pločevina

To finish off a base/plinth unit at the sides and for additional stability or interior configuration of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.

## Features

Št. Modela	VX 8640.044
Material	Jeklena pločevina
Barva	RAL 9005
Obseg dobave	Sestavni deli
Mere	Višina: 200 mm
Primerno za	Globina: = 800 mm
Tipska ocena po UL 50E	Type 1 Type 12
Teža/pakiranje	4,14 kg
Paketi	2 pc(s).
Neto teža	3,94 kg
Bruto teža	4,14 kg
Carinska tarifna številka	94039910
ETIM 9	EC000721
ECLASS 8.0	27182003
Opis izdelka	VX Base/plinth trim panel, side, H: 200 mm, for D: 800 mm, sheet steel

## Approvals

# Approvals

---

Approvals

UL + C-UL - FTTA